



### OPTIONS



### ACCESSORIES

- ZD-D28 Damper
- ZD-D40 Damper
- ZD-DF40 Damper

### VERSIONS

Type	Rated Power W	Rated Torque Ncm	Rated Current A	Peak Current A	Rated Voltage V	Rated Speed rpm	Torque Constant Ncm/A	Rotor Inertia gcm <sup>2</sup>	Length „A“ mm	Weight kg
DB42S01	31	5	0.88	2.63	48	6000	5.7	24	41	0.25
DB42S02	42	5	3.57	10.78	17	8000	1.4	24	41	0.25
DB42S03	26	6.25	1.79	5.4	24	4000	3.5	24	41	0.3
DB42M01	69	11	2.12	5.77	48	6000	5.2	48	60.3	0.45
DB42M02	62	7	1.63	4.88	48	8500	4.3	48	60.3	0.45
DB42M03	52	12.5	3.47	10.6	24	4000	3.6	48	60.3	0.45
DB42L01	75	18	5.14	15.5	24	4000	3.6	67	80.3	0.65
DB42C01	157	25	4.63	13.89	48	6000	5.4	89	100	0.75
DB42C02	147	10	3.57	10.71	48	14000	2.8	89	100	0.75
DB42C03	105	25	6.65	20	24	4000	3.76	89	100	0.75

### DIMENSIONS (IN MM)

