



### OPTIONS



### VERSIONS

Type	Rated Power W	Rated Torque Ncm	Rated Current A	Peak Current A	Rated Voltage V	Rated Speed rpm	Torque Constant Ncm/A	Rotor Inertia gcm <sup>2</sup>	Length „A“ mm	Weight kg
DF45S024050	30	5	1.58	4.8	24	5000	3.55	99	18	0.08
DF45M024053	50	8.4	2.36	7	24	5260	3.35	135	21.6	0.12
DF45L024048	65	13	3.26	9.5	24	4840	3.69	181	27	0.15

### ORDER IDENTIFIER



#### DF45S024050-

- A = PCB connector
- A2 = cable with connector

### ACCESSORIES



#### ZK-JST-PHR-6-0.3M


Hall Cable DF45 0.3 m

#### ZK-JST-VHR-5N-0.3M

Motor Cable DF45 0.3 m

### DIMENSIONS (IN MM)

#### DF45-A



### DIMENSIONS (IN MM)

DF45-A2

