BKE

Brake

CAUTION

Do not slow down the motor directly with the brake! In our standard configuration, the brake should only be used as a holding brake. If bought in combination with a motor, the brake must be mounted by Nanotec.

TECHNICAL DATA

Operating Voltage	24 VDC
Hub	borehole ... H8 with 2 grub screws AM3x4
Fastening	with 4 M3 screws
Connection	leads L=400 mm

VERSIONS

Type	Rated Power W	Holding Torque Ncm	Moment of Inertia kg mm²	Switch-On Time ms	Switch-Off Time ms	Size mm	Shaft Diameter mm	Weight kg
Brake-BKE-0,4-5,0	8	40	1.3	10	6	32	5	0.08
Brake-BKE-1,0-6,35	10	100	2.1	12	8	34	6.35	0.11
Brake-BKE-2,0-6,35	11	200	6,7	25	7	42	6.35	0.185

DIMENSIONS (IN MM)

BKE-0.4-5.0



DIMENSIONS (IN MM)

BKE-1.0-6.35



DIMENSIONS (IN MM)

BKE-2.0-6.35



BRAKES