


| Position | Designation 1 | Designation 2 | Quantity |
|----------|-------------------------------------|-----------------|----------|
| 10 | LAPP, ÖLFLEX 115CY, 3G1, shielded | Length: 10000mm | 1. |
| 20 | Heat shrink tube | Length: 40mm | 1 |
| 30 | Cable end sleeve, 1 mm ² | Isolated, 12mm | 3 |
| 40 | Crimp contacts | 7.010.982.002 | 3 |
| 50 | M16 Inserts, 3 pole | 7.003.983.102 | 1 |
| 60 | M16 right angle connector | 7.831.400.000 | 1 |

| TWINTUS-CONNECTOR 3 POLE | | |
|--------------------------|-------------------|-----------------|
| Wire No./Colour | Connector Pin No. | Function |
| 1 | 1 | +UB |
| 2 | 2 | GND |
| GN-YE | 3 | Protective Wire |

| | | | | | | | | | | |
|-----|------------------------------|----------|------|--|--|----------------------------------|-----------|--------------------------------------|----------|---------------|
| 5 | revise drawing | 25.08.16 | A.S. |  Nanotec PLUG & DRIVE | APVD | X.W. | 07.05.12 | M16 right angle connector with cable | | |
| 4 | Change Length | 21.02.14 | J.D. | | CHKD | | | | | |
| 3 | Chg. connector P/N+conn.view | 24.01.14 | J.D. | Surface specification DIN ISO 1302 | General tolerances DIN ISO 2768- cH | Work piece edge DIN ISO 13715 | DRN | J.W. | 07.05.12 | DWG.NO |
| REV | DESCRIPTION | DATE | DRN | | | | SIGNATURE | DATE | | ZK-TW-3-10M-2 |