



Position	Designation 1	Designation 2	Quantity
10	LAPP, ÖLFLEX 115CY, 3G1, shielded	Length: 10000mm	1.
20	Heat shrink tube	Length: 40mm	1
30	Cable end sleeve, 1 mm ²	Isolated, 12mm	3
40	Crimp Contacts	7.010.982.002	3
50	M16 Inserts, 3 pole	7.003.983.102	1
60	M16 Connector	7.810.400.000	1

TWINTUS-CONNECTOR 3 POLE		
Wire No./Colour	Connector Pin No.	Function
1	1	+UB
2	2	GND
GN-YE	3	Protective Wire

3	revise drawing	25.08.16	A.S.	 Nanotec PLUG & DRIVE	APVD	S.R.	15.04.12	POWER CABLE PD6-N		
2	Wire cross section, colour white	16.10.12	A.S.		CHKD					
1	Function for ASB motor removed.	28.08.12	J.W.	Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- cH	Work piece edge DIN ISO 13715	DRN	J.W.	15.04.12	DWG.NO
REV	DESCRIPTION	DATE	DRN				SIGNATURE	DATE		ZK-TW-3-10M